










Characteristics of the Standard Versions GN 331		
The tubular handles have the CE marking, low voltage guideline 2014 / 35 / EU		
Emergency stop	2 channel, normally closed contact	
1st button with 2 LED	Changeover contact	
	LED, red and green	
2nd button	Normally open contact	
Contact termination, Pin configuration	Plug M12x1, 12-pole	
Switching voltage / Switching current	max. 24 V DC / max. 0.5 A	
Operating voltage (LEDs)	24 V DC ±15% / 10 mA	
Protection class	Identification no. 1: IP 67 (in screwed condition) Identification no. 2: IP 54	
Button color	For each button a set of caps is included, in this colors: red, green, blue	
Additional Variations as Special Application		
Emergency stop	1 channel	
Number of buttons > 2 Button optional with	Normally open contact	
	Normally closed contact	
	Changeover contact	
Button with labelling area	