



**Type**

- E** With cover cap (tapped blind bore)
- D** Without cover cap (tapped through bore)

**Metric table**

d <sub>1</sub>	d <sub>2</sub> Thread Type E	d <sub>3</sub> Thread Type D	d <sub>4</sub>	d <sub>5</sub>	h <sub>1</sub>	h <sub>2</sub>	t		
25* 0.98	M 4	-	-	-	13 0.51	8 0.31	19 0.75	8 0.31	10 0.39
32 1.26	M 5	M 6	M 5	M 6	15 0.59	10 0.39	23 0.91	10 0.39	12 0.47
40 1.57	M 6	M 8	M 6	M 8	17 0.67	13 0.51	27 1.06	12 0.47	18 0.71
50 1.97	M 8	M 10	M 8	M 10	19 0.75	15 0.59	32 1.26	14 0.55	20 0.79
63 2.48	M 10	M 12	M 10	M 12	22 0.87	19 0.75	37 1.46	16 0.63	26 1.02
74 2.91	M 12	-	M 12	-	26 1.02	17 0.67	43.5 1.71	22 0.87	26 1.02
84 3.31	M 16	-	M 16	-	28 1.10	17 0.67	44 1.73	21 0.83	25 0.98

Dimensions in: millimeters - inches

\*Only available with black cover cap

**Specification**

- Five-lobed knob  
Plastic  
Technopolymer (Polypropylene PP)
  - Reinforced, shock-resistant
  - Temperature resistant up to 194 °F (90 °C)
  - Black, matte finish
- Insert  
Stainless steel AISI 303
- Color of the cover cap (only type E)
  - Black, RAL 9005, matte finish
  - Orange, RAL 2004, matte finish
  - Gray, RAL 7035, matte finish
  - Yellow, RAL 1021, matte finish
  - Blue, RAL 5024, matte finish
  - Red, RAL 3000, matte finish
  - Green, RAL 6017, matte finish
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

- **DSW**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

**Information**

These EN 5337.7 knobs are characterized by their 5 lobes and recessed grips. They not only give them an attractive design, but their shape also allows a high torque to be achieved.

see also...

- Five-Lobed Knobs EN 5337.2 (Brass / Steel Insert) → page 602
- Solid Five-Lobed Knobs EN 5337 (Phenolic Plastic) → page 596
- Solid Five-Lobed Knobs EN 5337.4 (Stainless Steel Insert) → page 606
- Softline Five-Lobed Knobs EN 5337.6 → page 610
- Five-Lobed Knobs EN 5337.7 with Loss Protection GN 111.7 → page 2046

How to order (Without cover cap)	1	Handle diameter d <sub>1</sub>
<b>EN 5337.7-50-M10-D</b>	2	Thread d <sub>3</sub>
	3	Type

How to order (With cover cap)	1	Handle diameter d <sub>1</sub>
<b>EN 5337.7-74-M12-E-DRT</b>	2	Thread d <sub>2</sub>
	3	Type
	4	Color of the cover cap