



3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

**Assembly instruction**

Two M12 threaded holes are required to mount the EN 651 fluid level indicators; for very small wall thicknesses, two holes of Ø 12.5 mm are required for mounting with nuts.

For a perfect seal, the screws should not be overtightened (max. 12 Nm). Recommended roughness of the sealing surface, Ra = 3 µm.

