



Inch | Metric



Inch table

Dimensions in: inches / millimeters							
1	2		3				
b	d		l ₁	h ₁	h ₂	l ₂	t
0.83 21	1/4 x 20	-	3.68 93.5	1.42 36	1.18 30	4.41 112	0.35 9
1.02 26	1/4 x 20	5/16 x 18	4.61 117	1.61 41	1.34 34	5.47 139	0.35 9
1.06 27	1/4 x 20	5/16 x 18	5.20 132	1.77 45	1.46 37	6.14 156	0.35 9
1.10 28	5/16 x 18	-	7.05 179	1.97 50	1.65 42	8.03 204	0.35 9

Metric table

Dimensions in: millimeters / inches							
1	2		3				
b	d		l ₁	h ₁	h ₂	l ₂	t
21 0.83	M 6	-	93.5 3.68	36 1.42	30 1.18	112 4.41	9 0.35
26 1.02	M 6	M 8	117 4.61	41 1.61	34 1.34	139 5.47	9 0.35
27 1.06	M 6	M 8	132 5.20	45 1.77	37 1.46	156 6.14	9 0.35
28 1.10	M 8	-	179 7.05	50 1.97	42 1.65	204 8.03	9 0.35

Specification

Handle

Nylon plastic

- Black, RAL 9005, matte finish ● SW
- Glass fiber reinforced
- Operating temperature up to 230 °F (110 °C)

Tapped inserts

Brass

RoHS

On request

- Additional colors
- Various metric and inch size fasteners and kit packaging

Further enhancing the ergonomic styling of our cabinet U-handles MF, we have developed the cabinet U-handles MFB to give this style a broader range of mounting possibilities.

see also...

	Page
MT Cabinet U-Handles	QVX
GN 565 Cabinet U-Handles	QVX

Technical Information

Strength Values	QVX
Plastic Characteristics	QVX

How to order (Inch)

MFB-27-1/4X20-132-SW

1	Handle width b
2	Thread d
3	Length l ₁
4	Color

How to order (Metric)

MFB-26-M8-117-SW

1	Handle width b
2	Thread d
3	Length l ₁
4	Color