



- 1 Type**
SG With star knob
SK With wing knob
ST With T-handle
RG With hollow knurled knob GN 7336
KG With wing knob
HG With lever
- 3 Hook version**
H1 Pivoting radius R = 28
- 5 Identification no.**
1 Without latch bracket
2 With latch bracket

Metric table

Dimensions in: millimeters - inches

Hook distance A	d		h	
	Type SG, RG, KG, HG	Type SK, ST	Type SG, RG, KG, HG	Type SK, ST
18 0.71	28 1.10	32 1.26	4 0.16	6 0.24

* Dimensions of the latch bracket, see page 1299

Specification

- Cam latch housing
Zinc die-cast
- Housing collar
 - Chrome plated finish **CR**
 - Powder coated
Black, RAL 9005, textured finish **SW**
- Hook / assembly hardware
Steel, zinc plated, blue passivated finish
- Operating elements
Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- Cover cap (Type RG, KG, and HG)
Plastic
Light gray, matte finish
- Protection class IP65
- IP Protection Classes → page XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

Information

GN 115.8 cam latches with hook and latch bracket are mainly used for sliding doors and flaps. The latching action is in a radial direction to the axis of rotation, resulting in a wide variety of different uses. The latches GN 115.8 are supplied with loosely enclosed hook.

see also...

- List of Cam Latch / Cam Lock Types → page 1256
- Cam Latches with Hook GN 115.8 (Operation with Socket Key) → page 1300
- Cam Locks with Hook GN 115.8 → page 1301

On request

- Cam latches with other hook distance A
- Hook with other pivoting radius R

How to order	
1	Type
2	Hook distance A
3	Hook version
4	Finish (Housing collar)
5	Identification no.

1 2 3 4 5
GN 115.8-HG-18-H1-SW-2