



Metric table

d ₁	h ₁	b	d ₂	d ₃	d ₄	d ₅	d ₆	h ₂	m	A/F	t min.
For rod / tube											
30 ^{+0.1 -0.25} 1.181 ^{+0.004 -0.01}	60 2.36	27.5 1.08	M 10	46 1.81	46.6 1.83	42 1.65	8 0.31	84 3.31	13.5 0.53	5	20 0.79
40 ^{+0.15 -0.3} 1.575 ^{+0.006 -0.012}	70 2.76	30 1.18	M 12	56 2.20	56.8 2.24	50 1.97	8 0.31	99 3.90	18.5 0.73	5	25 0.98

Specification

Handle leg	
Stainless steel AISI 304	NI
Ground, matte finish (Ra < 0.8 µm)	MT
Sealing ring / Wiper	
TPU	T
• Blue	
• Operating temperature -4 °F to +230 °F (-20 °C to +110 °C)	
• Hardness 95 ±5 Shore A	
• FDA compliant material	
Clamping wedge	
Brass	
Set screw	
Stainless steel	
RoHS	
Accessory	Page
GN 1580 Hex Head Screws	QVX
GN 1581 Hex Head Screws	QVX

Handle legs GN 3331 comply with the DGUV testing principles and are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the non-concave geometry prevent adherence of dirt and facilitate cleaning. The straight handle legs are designed for use with tubular handles GN 3330 to reduce large distances between mounting points or excessive loads on the handle legs. Regardless of the handle application, supports can be used to fix rods and tubes with the corresponding diameter d₁. The tube or rod is fastened during installation using the integrated clamping wedge.

see also...	Page
GN 3330 Tubular Handles (Stainless Steel, Hygienic Design)	QVX

Technical Information

Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1 Material
	2 Diameter d ₁
	3 Height h ₁
	4 Finish
	5 Sealing ring material

GN3331-NI-40-70-MT-T