




Metric table

1		2		Dimensions in: millimeters / inches						
d ₁	l ₁ ±0.5 Type A ±0.3 Type B Tapped hole for mounting stud	d ₂	d ₃	h ₁	h ₂	l ₂	r ≈	t ₁	t ₂	
20 0.79	200 7.87	200 7.874	M 8	-	105 4.13	68 2.68	20 0.79	22 0.87	15 0.59	-
20 0.79	300 11.81	300 11.811	M 8	-	105 4.13	68 2.68	20 0.79	22 0.87	15 0.59	-
28 1.10	250 9.84	250 9.843	M 10	32 1.26	128 5.04	90 3.54	20 0.79	32 1.26	-	17 0.67
28 1.10	350 13.78	350 13.780	M 10	32 1.26	128 5.04	90 3.54	20 0.79	32 1.26	-	17 0.67
28 1.10	500 19.69	500 19.685	M 10	32 1.26	128 5.04	90 3.54	20 0.79	32 1.26	-	17 0.67

Specification

Handle

- Stainless steel AISI 304
- d₁ = 20 mm: Solid material
 - d₁ = 28 mm: Tube Ø 28 x 2 mm
 - Matte shot-blasted finish

Tapped insert / Mounting stud

Stainless steel AISI 303

Set screw (Type B)

- Stainless steel
- d₁ = 20 mm: DIN 914-M5-6-NI
 - d₁ = 28 mm: DIN 914-M6-8-NI

RoHS

Cabinet U-handles GN 426.6 can be mounted from the back (type A) as well as from the operator's side (type B). In this case the stud is first screwed in from the machine side and then the handle is pushed on and secured with the set screw.

Both mounting methods allow the mounting of a pair of handles in opposite position. This method could be used e.g. on doors (double handle). In general, a mounting stud with special length l₂ might be required.

see also...	Page
GN 425.1 Cabinet U-Handles (Ø 8, 10, 12 mm, Offset Round Aluminum / Stainless Steel)	QVX

Technical Information	Page
Load Capacity Information	QVX
Stainless Steel Characteristics	QVX

How to order	1	Handle diameter d ₁
	2	Length l ₁
	3	Type
GN 426.6-20-300-A		