






Swivel width k=16




Front views for different bore Ø d



Swivel width k=30



Front views for different bore Ø d



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ d	² k
B 8	16 0.63
B 8	30 1.18
B 12	16 0.63
B 12	30 1.18

¹ d	² k
B 18	16 0.63
B 18	30 1.18
B 30	30 1.18

Specification

- Stainless steel AISI 304
Matte shot-blasted finish
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

GN 479 sensor brackets are designed for holding sensors that are attached with two lock nuts. The mounting hole matches the central thread of GN 478 attachment mounting clamps and GN 484 attachment swivel mounting clamps. For k = 30 mm, the cross-shaped slotted holes provide extra adjustability and allow the use of two mounting screws. Mounting screws have to be ordered separately.

see also...

- *Attachment Mounting Clamps GN 478* → page 1827
- *Attachment Swivel Mountings Clamps GN 484* → www.jwwinco.com

How to order GN 479-B12-16	¹ Bore d
	² Width k