



**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
1.69 42.9	5/16 x 18	0.67 17.0	1.14 29.0	0.43 10.9	0.55 14.0
2.09 53.1	3/8 x 16	0.75 19.0	1.34 34.0	0.51 13.0	0.67 17.0

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
43 1.69	M 6	M 8	17 0.67	11 0.43	12 0.47
53 2.09	M 8	M 10	19 0.75	13 0.51	17 0.67
66 2.60	M 10	M 12	21.5 0.85	15.5 0.61	17 0.67
77 3.03	M 12	-	26 1.02	21 0.83	20 0.79

**Specification**

- Five-lobed knob  
Plastic  
Technopolymer (Polypropylen PP)
- Softline coating
  - Elastomer (TPE) 70 shore A
  - Chemically bonded with the plastic core
  - FDA compliant plastic granulate
  - Temperature resistant up to 175 °F (80 °C)
  - Black, matte finish
- Color of the cover cap (matte finish):
 

● -	Black, RAL 9005
● DOR	Orange, RAL 2004
● DGR	Gray, RAL 7035
● DGB	Yellow, RAL 1021
● DBL	Blue, RAL 5024
● DRT	Red, RAL 3000
● DGN	Green, RAL 6017
- Tapped insert  
Brass
- *Plastic Characteristics* → page 2135
- RoHS compliant

**Information**

The Softline coating makes the GN 5337.6 five-lobed knobs particularly user-friendly and ergonomic. The **soft, slip-proof** contact area improves the contact both in hot (hand perspiration) and in dry ambient conditions, in the event of oily surfaces and even high or low temperatures. The use of five-lobed knobs is recommended particularly when heavy duty clamping is required.

see also...

- *Product Family Softline* → page 18

How to order (Inch, with black cover cap)	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
<b>EN 5337.6-1.69-5/16X18</b>		

How to order (Metric, with colored cover cap)	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
	3	Color of the cover cap
<b>EN 5337.6-53-M10-DRT</b>		