



Metric table

Dimensions in: millimeters - inches

d₁	d₂ Thread	Length l			d₃	h₁	h₂	t
32 1.26	M 5	10 0.39	20 0.79	40 1.57	14 0.55	26 1.02	16 0.63	10 0.39
32 1.26	M 6	10 0.39	20 0.79	40 1.57	14 0.55	26 1.02	16 0.63	12 0.47
40 1.57	M 6	10 0.39	20 0.79	40 1.57	16 0.63	30 1.18	17 0.67	12 0.47
40 1.57	M 8	16 0.63	30 1.18	50 1.97	16 0.63	30 1.18	17 0.67	14 0.55
50 1.97	M 8	16 0.63	30 1.18	50 1.97	19 0.75	35 1.38	19 0.75	14 0.55
50 1.97	M 10	20 0.79	30 1.18	50 1.97	19 0.75	35 1.38	19 0.75	16 0.63
60 2.36	M 10	20 0.79	30 1.18	50 1.97	22 0.87	41 1.61	22 0.87	16 0.63
60 2.36	M 12	20 0.79	30 1.18	50 1.97	22 0.87	41 1.61	22 0.87	18 0.71

Specification

- Triangular knob
Plastic
Technopolymer (Polyamide PA)
Temperature resistant up to
194 °F (90 °C)

- Color (shiny finish)
 - Black, RAL 9005 ● **SW**
 - Orange, RAL 2004 ● **OR**
 - (only available for tapped insert type)

- Tapped insert
Brass
- Threaded stud
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page 2135
- *RoHS compliant*

Information

EN 5339 triangular knobs offer an elegant shape and a bright finish.

How to order (Tapped insert)	1 Handle diameter d ₁
EN 5339-40-M8-OR	2 Thread d ₂
	4 Color

How to order (Threaded stud)	1 Handle diameter d ₁
EN 5339-50-M10-30-SW	2 Thread d ₂
	3 Length l
	4 Color