



Metric



SS
Stainless Steel

Metric table

2			3					Dimensions in: millimeters / inches		
d ₁	d ₂		d ₃	d ₄	l ₁	l ₂	l ₃			
	KU	KT								
18 0.71	M 6	M 6	10 0.39	15 0.59	40 1.57	12 0.47	2.5 0.10			
21 0.83	M 6	M 6	10 0.39	17 0.67	50 1.97	13 0.51	2.5 0.10			
23 0.91	M 8	M 8	13 0.51	19 0.75	65 2.56	14 0.55	2.5 0.10			
26 1.02	M 10	M 10	13 0.51	21 0.83	80 3.15	16 0.63	2.5 0.10			
28 1.10	M 10	M 10	13 0.51	22 0.87	90 3.54	16 0.63	2.5 0.10			
31 1.22	M 12	-	14 0.55	25 0.98	102 4.02	20 0.79	2.5 0.10			

Specification

Handle		1
• Plastic, Phenolic (PF)	KU	
- Operating temperature up to 230 °F (110 °C)		
- Black, shiny finish		
• Plastic, Polypropylene (PP)	KT	
- Operating temperature up to 176 °F (80 °C)		
- Black, matte finish		
Threaded spindle		
Stainless steel AISI 303		
RoHS		

Revolving handles GN 598.1 are used for decoupled transmission of a cranking motion to handwheels and cranked handles. The swivel-mounted handle body can be held firmly and safely while cranking. The internal hex is used as drive for screwing in. The revolving handles in version KU of phenolic resin have good resistance to chemical influences. The simple shape looks good in any environment.

see also...	Page
GN 598 Revolving Handles (Steel Threaded Spindle)	QVX
GN 598.5 Retractable Handles (with Locking Mechanism)	QVX
EN 598.2 Revolving Handles	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1	Material
	2	Handle diameter d ₁
	3	Thread d ₂
GN 598.1-KU-26-M10		