



Metric



elesa
Original design EBP.SAN



3 Type

B Mounting from the operator's side

Metric table

Dimensions in: millimeters / inches

1	2									
l_1	d_1	d_2	h_1	h_2	l_2	l_3 min.	s	A/F	t	
117 ±0.5 4.61 ±0.02	8.5 0.33	26 1.02	39 1.54	18 0.71	143 5.63	91 3.58	8.5 0.33	13	8.5 0.33	
179 ±1 7.05 ±0.04	8.5 0.33	29 1.14	51 2.01	19 0.75	208 8.19	150 5.91	9.5 0.37	13	16 0.63	

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature
-22 °F (-30 °C) to 266 °F (130 °C)
- Black-gray, RAL 7021, matte finish
- White, RAL 9016, matte finish

- SGA
- WSA

Cover cap

- Plastic, Polyamide (PA)
- Black-gray (for SGA)
- White (for WSA)

RoHS

On request

Various metric size fasteners and kit packaging

Bridge handles EN 628.1 are manufactured from an antimicrobial plastic. Adding a silver-based substance has created a natural active agent which helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antimicrobial effect of this additive will not diminish. Sterilizing at temperatures below 266 °F (130 °C) will also have no effect on the antimicrobial property.

With these properties, operating parts made of this plastic are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...	Page
EN 628 Bridge Handles (Mounting from the Back or from the Operator's Side)	QVX

Technical Information

Product Family Sanline	QVX
Product Family Ergostyle®	QVX
Strength Values	QVX
Plastic Characteristics	QVX

Accessory

EN 628.2 Spacers	QVX
------------------	-----

How to order

1 2 3 4
EN 628.1-117-8.5-B-SGA

- 1 Length l_1
- 2 Diameter d_1
- 3 Type
- 4 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

