



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	Length l ≈ GN 6336.4							Length l ≈ GN 6336.5					d ₃	h ₁	h ₂
		16	20	25	30	35	45	-	20	25	30	40	55			
32 1.26	M 6	0.63	0.79	0.98	1.18	1.38	1.77	-	-	-	-	-	12 0.47	20 0.79	9 0.35	
40 1.57	M 8	0.63	0.79	0.98	1.18	1.57	2.17	0.79	0.98	1.18	1.57	-	14 0.55	25 0.98	12 0.47	
50 1.97	M 10	0.98	1.18	1.38	1.77	2.17	-	0.79	0.98	1.18	1.77	2.17	18 0.71	32 1.26	15 0.59	
63 2.48	M 12	1.18	1.38	1.57	1.97	2.36	-	1.18	1.57	1.97	-	-	20 0.79	40 1.57	19 0.75	
80 3.15	M 16	1.18	1.57	1.97	2.36	2.76	-	-	-	-	-	-	25 0.98	50 1.97	23 0.91	

Specification

- GN 6336.4**
 - Threaded stud
Steel, blackened finish
 - Star knob
Cast iron, fettled and tumbled **SG**
- GN 6336.5**
 - Threaded stud
Stainless steel AISI 303
 - Star knob
Stainless steel
precision casting AISI CF-8 **ES**
Matte shot-blasted finish
 - Star knob
Aluminum, forged **AM**
Matte, tumbled finish **AP**
Polished finish **AP**
- For all types the threaded stud is screwed in and secured by a cross-dowel pin.
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Special inch and metric stud lengths and various stud tips

Information

GN 6336.4 cast iron star knobs extend the range of clamping applications and are perfect for medium to heavy duty clamping applications. GN 6336.5 star knobs have very good corrosion resistant properties.

see also...

- *Star Knobs GN 6336.4 (Plastic, with Steel Threaded Stud)* → page 578
- *Star Knobs GN 6336.5 (Plastic, with Stainless Steel Threaded Stud)* → page 578
- *Star Knobs GN 5334 / GN 5334.4 (Stainless Steel, with Threaded Stud)* → page 617

How to order (Steel threaded stud)	1 Material
GN 6336.4-SG-63-M12-50	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l

How to order (Stainless steel threaded stud)	1 Finish (Material)
GN 6336.5-AM-40-M8-25	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l