



**Metric table**



Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub> h9	d <sub>3</sub> H7	d <sub>4</sub>	d <sub>5</sub> +0.1	e	h min.	Length l -0.2	t	For side thrust pin Ø	
6 0.24	12 0.47	12 0.47	M 4	6.2 0.24	2 0.08	10 0.39	9.9 0.39	4.4 0.17	3 0.12	-
10 0.39	16 0.63	16 0.63	M 4	10.2 0.40	2 0.08	12 0.47	11.9 0.47	5.4 0.21	5 0.20	6 0.24
12 0.47	18 0.71	18 0.71	M 4	12.2 0.48	2 0.08	14 0.55	13.9 0.55	6.6 0.26	8 0.31	-
16 0.63	25 0.98	25 0.98	M 6	16.2 0.64	3 0.12	18 0.71	17.9 0.70	7.9 0.31	10 0.39	-

**Specification**

- Bushing  
Steel, blackened finish
- Set screw DIN 913  
Stainless steel, A2
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

**Information**

- GN 715.2 eccentric bushings facilitate the adjustment of GN 714 and GN 715 side thrust pins. By using this bushing, the spring loaded locating pin can be precisely located to suit the tolerance of the workpiece.
- see also...
- Press-Fit Side Thrust Pins GN 715 → page 1052
  - Press-Fit Side Thrust Pins GN 714 (Tapped Type) → page 1055

How to order

**GN 715.2-6**

1 Bore diameter d<sub>1</sub>