




Inch table

1

2

3

Dimensions in: inches - *millimeters*

d ₁	d ₂	Length l		d ₃	b	h ₁	h ₂
1.85 47.0	1/4 x 20	0.75 19.1		0.53 13.5	0.28 7.1	0.94 23.9	0.22 5.6
2.17 55.1	5/16 x 18	1.00 25.4		0.63 16.0	0.31 7.9	1.10 27.9	0.26 6.6
2.76 70.1	3/8 x 16	1.50 38.1		0.79 20.1	0.39 9.9	1.42 36.1	0.31 7.9

Metric table

1

2

3

Dimensions in: millimeters - *inches*

d ₁	d ₂	Length l			d ₃	b	h ₁	h ₂
40 1.57	M 5	16 0.63	20 0.79	-	13.5 0.53	6 0.24	20 0.79	4 0.16
40 1.57	M 6	20 0.79	30 1.18	-	13.5 0.53	6 0.24	20 0.79	4 0.16
40 1.57	M 8	20 0.79	30 1.18	40 1.57	13.5 0.53	6 0.24	20 0.79	4 0.16
48 1.89	M 6	20 0.79	30 1.18	-	13.5 0.53	7 0.28	24 0.94	5.5 0.22
48 1.89	M 8	20 0.79	30 1.18	40 1.57	13.5 0.53	7 0.28	24 0.94	5.5 0.22
55 2.17	M 8	20 0.79	30 1.18	40 1.57	16 0.63	8 0.31	28 1.10	6.5 0.26
63 2.48	M 10	20 0.79	30 1.18	-	19 0.75	9 0.35	32 1.26	7.5 0.30
70 2.76	M 10	20 0.79	30 1.18	40 1.57	20 0.79	10 0.39	36 1.42	8 0.31

Specification

- 4

• Wing body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, similar to RAL 7021, matte finish

• Threaded stud
Stainless steel AISI 303

• Color of the cover cap (matte finish)
Black-gray, RAL 7021
Orange, RAL 2004
Gray, RAL 7035
Yellow, RAL 1021
Blue, RAL 5024
Red, RAL 3000
Green, RAL 6017

●

DSG

●

DOR

●

DGR

●

DGB

●

DBL

●

DRT

●

DGN

• RoHS compliant

Information

The slightly concave identations on the ends of the EN 633.1 wing screws help to position the fingers to apply the maximum force when tightening.

Resistant to solvents, oils, grease and other chemical agents.

On request

- For certain minimum quantities, metric versions with brass threaded stud

How to order (Inch)	1 Handle diameter d ₁
	2 Thread d ₂
	3 Length l
	4 Color of the cover cap
EN 633.1-2.76-3/8X16-1.50-DSG	

How to order (Metric)	1 Handle diameter d ₁
	2 Thread d ₂
	3 Length l
	4 Color of the cover cap
EN 633.1-48-M6-30-DOR	