



Metric table

Dimensions in: millimeters / inches					
d ₁	d ₂	d ₃	h ₁	h ₂	t _{min.}
21 0.83	M 5	12.5 0.49	18 0.71	10.5 0.41	10 0.39
31 1.22	M 8	18.5 0.73	27 1.06	17 0.67	15 0.59

Specification

Knob

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature
 - 22 °F to +266 °F (-30 °C to +130 °C)
- Black-gray, RAL 7021, matte finish
- White, RAL 9016, matte finish

Tapped insert

Stainless steel AISI 303

SGA

WSA

RoHS

Knurled knobs EN 676 are manufactured from an antimicrobial plastic. Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antimicrobial effect of this additive will not diminish. Sterilizing at temperatures up to 266 °F (130 °C) will also have no effect on the antimicrobial property.

With these properties, operating parts made of this plastic are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...	Page
EN 676 Knurled Knobs (Plastic, with Brass Tapped Insert)	QVX
GN 676.1 Push / Pull Knobs (Steel, Blackened Finish)	QVX
GN 676.2 Push / Pull Knobs (Steel, Zinc Plated)	QVX
GN 676.5 Push / Pull Knobs (Stainless Steel)	QVX
GN 76 Mushroom Shaped Knobs	QVX

Technical Information	
Product Family Sanline	QVX
Product Family Ergostyle®	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	
1	Handle diameter d ₁
2	Thread d ₂
3	Color
EN 676-31-M8-SGA	