


Mounting example



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

Length l	s			b	d ₁	d ₂	m ₁	m ₂	m ₃
60	0.5	1	2	30	6.5	4.2	46	8	28
2.36	0.02	0.04	0.08	1.18	0.26	0.17	1.81	0.31	1.10

Specification

- Stainless steel AISI 304 **NI**
Matte, tumbled finish **MT**
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Other plate thicknesses

Information

Tolerances of chamfers, different sheet metal thicknesses, or the use of seals could mean that the mounting surfaces of multiple-joint hinges on the frame and door are not at the desired distance to each other.

GN 7247.2 spacer plates are designed as accessories for GN 7241, GN 7243 and GN 7247 multiple-joint hinges. They allow for adjustment in the third plane during assembly. Shimmed individually or in combination, they ensure the appropriate position or height compensation on the mounting flanges.

The holes d₂ are used to accommodate clamping or positioning pins, making it easy to position the spacer plates and the multiple-joint hinges.

see also...

- Spacer Plates with Tapped Holes GN 7247.4 → page 1397
- Mounting Plates with Threaded Studs GN 7247.6 → page 1398
- Multiple-Joint Hinges GN 7241 (Opening Angle of 90°) → page QVX
- Multiple-Joint Hinges GN 7243 (Opening Angle of 120°) → page QVX
- Multiple-Joint Hinges GN 7247 (Opening Angle of 180°) → page QVX

How to order	1	Material
	2	Length l
	3	Width s
	4	Finish
GN 7247.2-NI-60-1-MT		