




Metric table

1	2	3	Dimensions in: millimeters / inches		
l ₁	d ₁	l ₂	d ₂	h ₁	h ₂ ≈
44* 1.73	M 6	20 0.79	10 0.39	8.5 0.33	32 1.26
63 2.48	M 6	20 0.79	10 0.39	9 0.35	40 1.57
63 2.48	M 8	25 0.98	13 0.51	13.5 0.53	44 1.73
78 3.07	M 8	25 0.98	13 0.51	14.5 0.57	52 2.05

* This size is only available in version SG

Specification

Lever body

- Plastic, Polyamide (PA)
 - Glass fiber reinforced
 - Operating temperature
-22 °F to 266 °F (-30 °C to 130 °C)
 - Color
 - Black-gray, RAL 7021, matte finish
 - Blue, RAL 5005, matte finish
- SG

● VDB
- FDA compliant material
- Visually detectable

Serrated ring

Zinc die-cast

Threaded insert / Retaining screw

Stainless steel AISI 303

RoHS

For plastic clamp connectors, adjustable levers GN 911.9 replace the hex socket cap screws DIN 912, the clamping point or the joint axis. The table of dimensions of the plastic connector clamps shows the matching levers for each screw location. The plastic used in version VDB is made from blue, visually detectable and FDA compliant plastic granulate as per FDA CFR.21 and EU 10/2011.

Technical Information	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1 Length l ₁
	2 Thread d ₁
	3 Thread length l ₂
	4 Color
GN911.9-63-M8-25-SG	