




Metric table

2

d				h	A/F
Fine thread		Pipe thread			
Steel	Stainless steel NI / A4	Steel	Stainless steel NI / A4		
M 6 x 1	-	-	-	6 0.24	3 0.12
M 8 x 1	M 8 x 1	-	-	8 0.31	4 0.16
M 10 x 1	M 10 x 1	R 1/8	R 1/8	8 0.31	5 0.20
M 12 x 1.5	M 12 x 1.5	-	-	10 0.39	6 0.24
M 14 x 1.5	M 14 x 1.5	R 1/4	R 1/4	10 0.39	7 0.28
M 16 x 1.5	M 16 x 1.5	-	-	10 0.39	8 0.31
M 18 x 1.5	M 18 x 1.5	R 3/8	R 3/8	10 0.39	8 0.31
M 20 x 1.5	M 20 x 1.5	R 1/2	R 1/2	10 0.39	10 0.39
M 22 x 1.5	M 22 x 1.5	-	-	10 0.39	10 0.39
M 24 x 1.5	M 24 x 1.5	-	-	12 0.47	12 0.47
M 26 x 1.5	-	R 3/4	R 3/4	12 0.47	12 0.47
M 30 x 1.5	-	R 1	R 1	12 0.47	17 0.67
M 36 x 1.5	-	-	-	15 0.59	19 0.75
M 42 x 1.5	-	R 1 1/4	-	18 0.71	22 0.87
M 45 x 1.5	-	-	-	18 0.71	22 0.87
M 48 x 1.5	-	R 1 1/2	-	20 0.79	24 0.94

Dimensions in: millimeters / inches

1

Specification	
Body	
• Steel, zinc plated, blue passivated finish	ST
• Stainless steel AISI 303	NI
• Stainless steel AISI 316Ti	A4
Thread coating (Type GPC)	
Precote 5	
• White	
• Operating temperature	
-76 °F to +302 °F (-60 °C to +150 °C)	

RoHS

Threaded plugs DIN 906 are used to close bore holes with cylindrical internal thread.

The tightness depends on the material, the pressure, the temperature as well as the material pairing. The version with GPC thread coating provides a higher degree of safety.

see also...

GN 749 Threaded Plugs (Steel)

DIN 908 Threaded Plugs (Steel)

DIN 910 Threaded Plugs (with Collar and External Hex)

Page

QVX

QVX

Technical Information

GPC Thread Coating (Precote 5)

Stainless Steel Characteristics

QVX

QVX

How to order

1

2

3

DIN 906-ST-M36X1.5-GPC

1 Material

2 Fine thread d (Pipe thread d)

3 Type

www.jwwinco.com | 1-800-877-8351

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

1