


Application example



Inch table

Dimensions in: inches - millimeters

¹ d_1	² d_2 Thread	d_3	h_1	h_2
1.00 25.4	1/4 x 20	0.50 12.7	0.88 22.4	0.50 12.7
1.50 38.1	5/16 x 18	0.63 16.0	0.88 22.4	0.38 9.7
2.00 50.8	3/8 x 16	0.81 20.6	1.00 25.4	0.50 12.7
2.50 63.5	1/2 x 13	1.00 25.4	1.13 28.7	0.56 14.2

Specification

- Solid aluminum extrusion 6063-T5, etched and clear anodized finish
- RoHS compliant

On request

- Metric sizes

Information

CKSQ quick release hand knobs are used in such applications where the knob has to be completely removed after the releasing operation and mounted again rapidly for re-clamping.

The knob is tilted over the threaded spindle. When in position, the knob is brought into a straight position for mating of the two threads on the insert and spindle. The knob will then have to be turned only by a fraction of a rotation to achieve clamping.

Lightweight yet a good choice for medium-duty clamping applications.

see also...

- Hand Knobs CKS (with Tapped or Plain Bore, or Blank Type) → page 636

How to order	¹ Handle diameter d_1
CKSQ-2.00-3/8X16	² Thread d_2

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4