



**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> l <sub>1</sub>	<sup>3</sup> d <sub>2</sub> Slip fit	<sup>4</sup> d <sub>3</sub>	l <sub>2</sub>	s	d <sub>4</sub>
1/4 x 20	2.00 50.8	3/16	0.50 12.7	0.75 19.1	0.25 6.4	0.25 6.4
1/4 x 20	3.00 76.2	3/16	0.50 12.7	1.25 31.8	0.25 6.4	0.25 6.4
5/16 x 18	3.00 76.2	1/4	0.63 16.0	1.50 38.1	0.31 7.9	0.31 7.9
5/16 x 18	3.00 76.2	5/16	0.63 16.0	1.50 38.1	0.31 7.9	0.31 7.9
5/16 x 18	4.00 101.6	1/4	0.63 16.0	2.00 50.8	0.31 7.9	0.31 7.9
5/16 x 18	4.00 101.6	5/16	0.63 16.0	2.00 50.8	0.31 7.9	0.31 7.9
3/8 x 16	3.00 76.2	5/16	0.75 19.1	1.50 38.1	0.38 9.7	0.38 9.7
3/8 x 16	3.00 76.2	3/8	0.75 19.1	1.50 38.1	0.38 9.7	0.38 9.7
3/8 x 16	3.75 95.3	3/8	1.00 25.4	1.50 38.1	0.50 12.7	0.38 9.7
3/8 x 16	3.75 95.3	3/8	0.75 19.1	2.00 50.8	0.38 9.7	0.38 9.7
3/8 x 16	5.00 127.0	5/16	0.75 19.1	2.50 63.5	0.38 9.7	0.38 9.7
3/8 x 16	5.00 127.0	3/8	0.75 19.1	2.50 63.5	0.38 9.7	0.38 9.7
3/8 x 16	5.00 127.0	3/8	1.00 25.4	2.50 63.5	0.50 12.7	0.50 12.7
1/2 x 13	3.75 95.3	3/8	1.00 25.4	1.50 38.1	0.50 12.7	0.50 12.7
1/2 x 13	5.00 127.0	3/8	1.00 25.4	2.00 50.8	0.50 12.7	0.50 12.7
5/8 x 11	4.50 114.3	5/8	1.25 31.8	2.00 50.8	0.63 16.0	0.63 16.0
5/8 x 11	6.00 152.4	5/8	1.25 31.8	2.50 63.5	0.63 16.0	0.63 16.0
3/4 x 10	4.50 114.3	3/4	1.50 38.1	2.00 50.8	0.75 19.1	0.75 19.1
3/4 x 10	6.00 152.4	3/4	1.50 38.1	2.50 63.5	0.75 19.1	0.75 19.1

**Specification**

- Cold finished low carbon steel
  - Hardened
  - Blackened finish
- RoHS compliant

**Information**

SEB swing bolts are mainly used for jigs or fixtures and for applications that require linkages to an item, such as connecting a swing bolt to a cylinder yoke, for example.

How to order		<sup>1</sup> Thread d <sub>1</sub>
<sup>1</sup>	<sup>2</sup>	<sup>2</sup> Length l <sub>1</sub>
<b>SEB-1/4X20-2.00-3/16-0.50</b>		<sup>3</sup> Slip fit d <sub>2</sub>
<sup>4</sup>		<sup>4</sup> Diameter d <sub>3</sub>

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

