



Pneumatic Fastening Clamps

Mounting Methods / Accessories




The mounting holes on the main body of the pneumatic fastening clamps have been designed to allow installation direct on the tapped holes or alternatively with through bolts.

Centering guide bushings
GN 870




Centering guide bushings present an important function when mounting the pneumatic fastening clamps: they absorb lateral thrust and they ensure a precise alignment.



Mounting of the cylinder by a mounting bracket increases the numerous ways they can be installed.

Even mounting brackets use centering guide bushings for precise positioning.


Clamping arms




There is an extensive range of accessories available for pneumatic fastening clamps, such as tool holders (clamping arms) for thrust bolts and jaw blocks. The sketches shown on the right give some idea.

The combination of clamping tools on the clamping arm and brackets represent together a tool set.

Jaw blocks



For mounting and precise positioning of clamping arms and jaw blocks, GN 870 centering guide bushings are also used. The individual data sheets give further information.



All pneumatic fastening clamps can be fitted with sensors to monitor the end position of the stroke.

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

